

Filters position 1 DAPI/FITC/TRITC

Filterset type

Sedat (multi-band dichroic, sin ▾)

Channels

- DAPI/FITC
- DAPI/FITC/TRITC
- DAPI/FITC/TRITC #2
- DAPI/FITC/TRITC #3
- DAPI/FITC/TRITC/Cy5
- DAPI/FITC/Texas Red

Include light sources

Show filterset details

Fluorescent dyes

- Texas Red
- Texas Red dextran
- Texas Red DHPE
- TRITC
- Venus
- YFP


Unselect

Wavelength range

350 nm - 750 nm

- Excitation filters
- Dichroic mirror
- Emission filters
- Light sources & dyes
- Band reserved for QPI (642-676 nm)

Click on any legend item to



Filters position 2 GFP/mCherry

Filterset type

Sedat (multi-band dichroic, sin)

Channels

- CFP/YFP
- CFP/YFP/mCherry
- CFP/YFP/mCherry #2
- GFP/DsRed
- GFP/mCherry**
- GFP/mCherry #2

Include light sources

Show filterset details

Fluorescent dyes

- Texas Red
- Texas Red dextran
- Texas Red DHPE
- TRITC
- Venus
- YFP

Unselect

Wavelength range

350 nm - 750 nm

- Excitation filters
- Dichroic mirror
- Emission filters
- Light sources & dyes
- Band reserved for QPI (642-676 nm)

Click on any legend item to hide/show its

